






6 5 4 3 2 1

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/20/16	



RECOMMENDED PCB LAYOUT

HEX NUT	BRASS	GOLD
WASHER	STEEL	GOLD
CONTACT PIN	BRASS	GOLD
INSULATOR	PTFE	WHITE
BARREL	BRASS	GOLD
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Nominal Impedance: 50 ohms
Frequency range: DC 0–18 GHz
Working voltage: 335 Volts max
Proof voltage: 1000 Volts
Temperature Rating:
Operating temperature: –65°C to +165°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010		ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
		TITLE SMA JACK EDGE CARD MOUNT PCB, STRAIGHT	
APPROVALS	DATE	SIZE	PART NO.
DRAWN	HR	X	RF2-152-T-00-50-G-HDW
CHECKED	MW		
APPROVED		REF: S00277T	SCALE: NTS
			SHEET 1 OF 1