





APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

| Rev | AWO # | Description | Date    | Appr |
|-----|-------|-------------|---------|------|
| -   |       | RELEASED    | 8/10/21 |      |



RECOMMENDED  
PANEL CUT-OUT



CIRCUIT DIAGRAM  
(DPST)

SW-T1-3X-E-K2  
 A=ON-OFF  
 C=OFF-(ON)

# SPECIFICATIONS:

## Material:

Body: Bakelite, Color: Black

Lever: Brass, Nickel plated

Terminal: Brass, Silver plated

## Electrical:

Rating: 10A @ 250V AC

15A @ 125V AC

Contact resistance: 50 mΩ max

Insulation resistance: 1000 MΩ min (500VDC)

Dielectric withstanding voltage: 1500V AC for 1 minute

Electrical Life: 10,000 cycles

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS  
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

| INCHES      | HOLES       |
|-------------|-------------|
| .X ± .10    | ØX ± .10    |
| .XX ± .020  | ØXX ± .015  |
| .XXX ± .015 | ØXXX ± .010 |

|          |    |         |
|----------|----|---------|
| DRAWN    | WX | 8/10/21 |
| CHECKED  | RC | 8/10/21 |
| APPROVED |    |         |

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY  
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN  
PERMISSION FROM ADAM TECH

**ADAM  
TECH**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE SWITCH, TOGGLE MEDIUM, DPST,  
ON-OFF, OFF-(ON), PC TERMINAL .250" [6.35MM]

|              |                           |              |
|--------------|---------------------------|--------------|
| SIZE<br>X    | PART NO.<br>SW-T1-3X-B-K2 | REV.<br>-    |
| REF: S00204C | SCALE: NTS                | SHEET 1 OF 1 |