







APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/20	



Z= Latching
S= Momentary
SW-PB7-1X-A-RX-H-X-G2A



	LED Color
Blank	Standard Black
W	White
R	Red
G	Green
Y	Yellow (Amber)
B	Blue
S	Silver
RG	Red/Green
RY	Red/Yellow
RB	Red/Blue
RW	Red/White
GB	Green/Blue
RGB	Red/Green/Blue
RGY	Red/Green/Yellow
RGW	Red/Green/White
RBY	Red/Blue/Yellow
RBW	Red/Blue/White

	LED Voltage
1	3V
2	6V
3	12V
4	24V
5	48V
6	110V
7	220V

SPECIFICATIONS:

Material:
The crust material: Stainless steel, Copper plated Nickel
Electrical:
Switch Rating: 5A, 250VAC
Contact resistance: 30 mΩ max
Insulation resistance: 100 Mohms min (500VDC)
Dielectric withstanding voltage: 2000 VAC
Temperature Rating:
Operating temperature: -25°C to +55°C
Environmental:
Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	OW	11/23/20
CHECKED	AC	11/23/20
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		SWITCH, ANTI-VANDAL, SPST, 19MM SOLDER TYPE, RING ILLUMINATED	
SIZE X	PART NO. SW-PB7-1X-A-RX-H-X-G2A	REV. -	
REF: S00206C	SCALE: NTS	SHEET 1 OF 1	