

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/30/21	

APPROVED: _____

DATE: _____ TITLE: _____

D

D

C

C

B

B

SPECIFICATIONS:

Material:

Movable Contact: Copper Alloy, Silver Plated

Terminal: Copper Alloy, Silver Plated with outer layer in gold plating

Electrical:

Voltage rating: 120VAC or 38VDC

Current rating: 1 Amps

Contact resistance: 10 mΩ max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500V RMS @Sea level

Mechanical:





Waterproof: IP68

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Lead free, RoHS compliant

CIRCUIT DIAGRAM
(DPDT) ON-MOMENTARYUNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø X ± .10
.XX ± .020	Ø XX ± .015
.XXX ± .015	Ø XXX ± .010

DRAWN JJ 9/30/21

CHECKED RC 9/30/21

APPROVED

ADAM
TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
PUSHBUTTON SWITCH, ON-MOMENTARY, DPDT
GOLD OVER SILVER PLATED, PCB TYPE, IP68

SIZE	PART NO.	REV.
X	SW-PB8-BA00B2GE-2D	-
REF: S00198T	SCALE: NTS	SHEET 1 OF 1