





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/18/20	



RECOMMENDED
 PANEL CUT-OUT



SPECIFICATIONS:

Material:

Body: PA66, Color: Black

Lever: Brass, Nickel plated

Terminal: Brass, Silver plated

Electrical:

Rating: 1.5A @ 250V AC

3A @ 125V AC

Contact resistance: 20 mΩ max

Insulation resistance: 1000 MΩ min (500VDC)

Dielectric withstanding voltage: 1000V AC for 1 minute

Electrical Life: 10,000 cycles

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ØX ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010			ADAM TECH		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE			
DRAWN		OW	11/18/20			
CHECKED		AC	11/18/20			
APPROVED						
TITLE			SWITCH, TOGGLE SUB-MINIATURE, SPST, ON-OFF, SOLDER TYPE			
SIZE X		PART NO. SW-T3-1A-A-A3-S1		REV. -		
REF: -		SCALE: NTS		SHEET 1 OF 1		