




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/7/05	
A		REDRAWN	7/13/11	
B		UPDATE SPEC.	12/4/19	AY/LW



SPECIFICATIONS:

Material:

Insulator: Nylon 66

Insulator color: Black

Contact: Brass, Tin plated

Screw: Steel, M3, Nickel plated

Electrical:

Voltage rating: 300 VAC.

Current rating: 10 Amp.

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Mechanical:

Screw Torque Value: 10 Kg-cm

Wire range: 16 - 22 AWG STR

Temperature Rating:

Operating temperature: -40°C to +120°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 32

A = .250 [6.35] x No. of Positions + .049±.031 [1.25±0.80]

B = .250 [6.35] x No. of Spaces ±.020 [0.50]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS DATE

DRAWN SS 6/7/05

CHECKED

APPROVED

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.250 [6.35] CENTERLINE BARRIER BLOCK
VERTICAL, PCB TAILS, BARRIER ENDS

SIZE X PART NO. TBA-XX-01-B REV. B

REF: S00031T SCALE: NTS SHEET 1 OF 1