






Rev	AWO #	Description	Date	Appr
-		RELEASED	5/12/10	

APPROVED: _____
DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT
(TOP VIEW)

SPECIFICATIONS:
Material:
Insulator: PBT, glass filled, rated UL 94V-0
Insulator color: White
Contacts: Phosphor Bronze
Shell: SPCC, Nickel plated
Plating:
Gold flash over Nickel underplate on contact area,
Tin over Copper underplate on PCB tails
Electrical:
Operating voltage: 30 VAC
Current rating: 1.5 Amp @ 250V AC
Contact resistance: 30 mohms max
Insulation resistance: 1000 Mohms min
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -20°C to +60°C
Environmental:
Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

USB, TYPE B, SINGLE PORT, RIGHT ANGLE,
THRU-HOLE, COLOR WHITE, SPCC SHELL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
APPROVALS				DATE			
DRAWN	DY	5/12/10					
CHECKED							
APPROVED							
SIZE	PART NO.	USB-B-S-RA-WT-SPCC		REV.			
X				-			
REF:	S00015C	SCALE:	NIS	SHEET	1 OF 1		