

6

5

4

3



2

1


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				



(Conn. TYPE)




DETAIL A

PACKING DIRECTION

REELING ANGLE
165°~180°

DIRECTION OF UNREELING



DETAIL A

REEL


330mm

100mm

For SIP

For CmK/Cpk

24.5mm

11 REEL/CARTON
4950 PCS/CARTON

DRYING AGENT

FITTING TAPE

Carton

TRIANGLE CYLINDER

CARDBOARD

300mm

350mm

350mm



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED		
MM	MM	ANGLE
0. ± 0.50		±5°
.0 ± 0.30		
.00 ± 0.20		

DRAWN	OW	7/23/20
CHECKED	JL	7/23/20
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE USB 4.0, TYPE C, FEMALE, RIGHT ANGLE,
40Gbps, BLACK INSULATOR, GOLD PLATED

SIZE X	PART NO. USB-C40-S-RA-BK-30-T/R	REV. A
REF: S00013T	SCALE: NTS	SHEET 2 OF 2

- 1.Fill in a corrugated paper board
- 2.Put 4 triangle cylinder cardboard in all corner.
- 3.Put 11 reels of products into water proof bag, with 4pcs of drying agent.
- 4.Cover with corrugated paper board.

6

5

4

3

2

1