


APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/21/15	
A		UPDATED DRAWING	9/14/17	HR/TY



**SPECIFICATIONS:**

**Material:**

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Copper Alloy, nickel plated

**Plating:**

30u" Gold over Nickel underplate on contact area,

Tin over Copper underplate on PCB tails

**Electrical:**

Voltage rating: 30 VAC

Current rating: 1.5 Amp

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC

**Temperature Rating:**

Operating temperature: -20°C to +60°C

**Environmental:**

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10    Ø.X ± .10 .XX ± .020    Ø.XX ± .015 .XXX ± .015    Ø.XXX ± .010			<b>ADAM TECH</b> 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS			DATE		
DRAWN	AY		1/21/15	TITLE	
CHECKED	GC		1/21/15	UNIVERSAL SERIAL BUS, SINGLE PORT VERTICAL, PCB, 30u" SEL GOLD PLATED	
APPROVED				SIZE	PART NO.
				X	USB-B-S-VT-HT-30
REF: S00005C			SCALE: NTS	SHEET 1 OF 1	