


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/1/12	
A		UPDATED DRAWING	9/14/17	HR/TY



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shell: Copper Alloy, nickel plated

Plating:

Gold flash over Nickel underplate on contact area, Tin over

Copper underplate on PCB tails

Electrical:

Voltage rating: 30 VAC

Current rating: 1.5 Amp

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

Operating temperature: -20°C to +60°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN AY CHECKED CC APPROVED			DATE 8/1/12 8/1/12		
TITLE UNIVERSAL SERIAL BUS SINGLE PORT, VERTICAL, PCB			SIZE X	PART NO. USB-B-S-VT-HT	REV. A
REF: S00005C			SCALE: NTS	SHEET 1 OF 1	