



APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/31/09	
A		UPDATED DRAWING	8/14/18	AY/MY



SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Blue

Contacts: Phosphor Bronze

Shell: SPCC, Nickel plated

Plating:

Gold flash over Nickel underplate on contact area,

Tin over Nickel underplate on Solder tails.

Electrical:

Voltage rating: 30 V

Current rating: 1.8 Amp for Pin1 & Pin4

0.25 Amp for Other contacts

Contact resistance: 30 mohms max for Pin1& Pin4

50 mohms max for Other contacts

Insulation resistance: 100 Mohms min

Dielectric withstanding voltage: 100 VAC (RMS)

Temperature Rating:

-20°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS

DATE

DRAWN	DY	3/31/09
-------	----	---------

CHECKED		
---------	--	--

APPROVED		
----------	--	--

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

USB 3.0 STANDARD B PLUG, SOLDER TYPE

SIZE

X

PART NO.

USB-BP3-S

REV.

A

REF: S00005C

SCALE: NTS

SHEET 1 OF 1