



Representative Image

Alternate Catalog No. AF12B-30-01RT-14

Catalog No. 1SBL157060R1401

Description: AF12B-30-01RT-14 250-500V50/60HZ-DC Contactor

UPC No 3471523125643

Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors

AF12B..RT 3-pole contactors comply with the latest railway rolling stock standards and allow installation in passengers or driver cabins for trains frequently operating tunnels or undergrounds. They are mainly used for controlling 3-phase motors and power circuits up to 690 V AC and 220 V DC. Improve the compactness of the installations thanks to reduced dimension and side-by-side mounting requiring less 15% width (without spacing) from -40 °C up to +70 °C. Meet all main rolling stocks standards: IEC 60947-4-1, IEC 60947-5-1, IEC 60077-1-2 and applicable parts of EN 50155 standards, shocks and vibration withstand conforming to IEC 61373 cat. 1, class B. Reach the highest levels in fire and smoke behaviour with compliance to European standard EN 45545-2 (HL2, HL3 hazard levels) in group mounting. Reduce train energy with lighter devices and requiring 68% less coil energy consumption in operation. Electronic coil interface accepting sinusoidal AC 50/60 Hz control supplies included inside Ucmin.... Ucmax voltage range. Max permitted AC 50/60 Hz control voltage must not be exceeded (see technical data). Wide range of auxiliary contact blocks for front and side mounting.

Descriptors

| | |
|----------------------|------------------|
| Category | AF Contactors |
| Block Contactor Type | 3-Pole Contactor |

Specifications

| | |
|---------------------------------------|---|
| Product Type | AF |
| General Use Rating UL/CSA | (600 V AC) 28 A |
| Object Classification Code | Q |
| Terminal Type | Ring-Tongue Terminals |
| Rated Control Circuit Voltage | 50 Hz /60 Hz DC Operation 250 ... 500 V |
| Number of Main Contacts NO | 3 |
| Number of Main Contacts NC | 0 |
| Climatic Withstand | Category B according to IEC 60947-1 Annex Q |
| Number of Auxiliary Contacts NO | 0 |
| RoHS Status | Following EU Directive 2011/65/EU |
| Rated Operational Voltage | Auxiliary Circuit 690 V Main Circuit 690 V |
| Number of Auxiliary Contacts NC | 1 |
| Rated Operational Current AC-1 | (690 V) 40 °C 28 A (220 ... 240 V AC) Three Phase 3 hp (440 ... 480 V AC) Three Phase 7-1/2 hp (550 ... 600 V AC) Three Phase 10 hp (120 V AC) Single Phase 1 hp (200 ... 208 V AC) Three Phase 3 hp (240 V AC) Single Phase 2 hp |
| Horsepower Rating UL/CSA | acc. to IEC 60947-5-1, q = 40 °C 16 A |
| Conventional Free-air Thermal Current | (220 / 240 V) 4 A (24 / 127 V) 6 A (500 V) 2 A (690 V) 2 A (400 / 440 V) 3 A |
| Rated Operational Current AC-15 | Auxiliary Circuit 50 Hz Auxiliary Circuit 60 Hz Main Circuit 50Hz Main Circuit 60 Hz |
| Rated Frequency | |

Specifications

| | |
|--|--|
| Rated Short-time Withstand Current | for 0.1 s 140 A for 1 s 100 A |
| Rated Operational Current AC-3 | (380 / 400 V) 60 °C 12 A |
| Maximum Electrical Switching Frequency | AC-15 1200 cycles per hour DC-13 900 cycles per hour |
| Operate Time | Between Coil De-energization and NC Contact Closing 13 ... 98 ms Between Coil De-energization and NO Contact Opening 11 ... 95 ms Between Coil Energization and NC Contact Opening 38 ... 90 ms Between Coil Energization and NO Contact Closing 40 ... 95 ms |
| Rated Operational Current DC-13 | (125 V) 0.55 A / 69 W (24 V) 6 A / 144 W (250 V) 0.27 A / 68 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (220 V) 0.27 A / 60 W (400 V) 0.15 A / 60 W (500 V) 0.13 A / 65 W (600 V) 0.1 A / 60 W |
| Screw Terminal Type | Ring-Tongue Terminals |

Classifications

| | |
|----------|---|
| ETIM 4 | EC000066 - Magnet contactor, AC-switching |
| ETIM 6.0 | EC000066 - Power contactor, AC switching |
| ETIM 7 | EC000066 - Power contactor, AC switching |
| ETIM 5.0 | EC000066 - Magnet contactor, AC-switching |

Dimensions

| | |
|----------------------------|--------|
| Product Net Weight | 0.32kg |
| Product Net Depth / Length | 77 mm |
| Product Net Width | 45 mm |
| Product Net Height | 86 mm |

Package Information

| | |
|--------------------------------|---------------|
| Package Level 1 Width | 87 mm |
| Package Level 1 Height | 47 mm |
| Package Level 1 Depth / Length | 79 mm |
| Package Level 1 EAN | 3471523125643 |
| Package Level 1 Units | box 1 piece |
| Package Level 2 Width | 250 mm |
| Package Level 2 Height | 315 mm |
| Package Level 1 Gross Weight | 0.32 kg |
| Package Level 2 Units | 27 piece |
| Package Level 3 Units | 1296 piece |
| Package Level 2 Depth / Length | 300 mm |
| Package Level 2 Gross Weight | 17.28 kg |

Ordering

| | |
|------------------------|----------|
| Minimum Order Quantity | 1 |
| Customs Tariff Number | 85364900 |

