



Representative Image

Catalog No. TH3362SS316**Description: 60A 3P HD N4X SS316 600V FUSIBLE****UPC No 783164382327****Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty**

Designed for commercial and industrial applications where safety, high performance and continuity of service are essential. Listed to UL standard 98 enclosed and dead front switches. Suitable for use as service equipment when installed in accordance with the National Electrical Code. Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches. Meets or exceeds NEMA KS1 standard for enclosed switches, type HD. Fusible and non-fusible switches available (consult BuyLog for interrupt ratings). Quick-make, quick-break mechanism. 60/75 C conductor rating. Full cover interlocks. NEMA type 4X enclosure grade 316 stainless steel. TH3362SS

Descriptors

| | |
|-------------|------------|
| Category | Heavy Duty |
| GO Schedule | S1 |

Specifications

| | |
|---------------------------|---------------------------|
| Voltage | 600 AC |
| Amperage | 60 A |
| Poles | 3 |
| Wires | 3 |
| Fusing | Fusible |
| Enclosure | NEMA 4/4X (316 Stainless) |
| Options | None |
| Wire Range (Cu/Al) | 14-2 |
| 480 Vac, NEC Std, 1-ph | 5 |
| 480 Vac, NEC Std, 3-ph | 15 |
| 480 Vac, Time Delay, 1-ph | 20 |
| 480 Vac, Time Delay, 3-ph | 30 |
| 600 Vac, NEC Std, 1-ph | 3 |
| 600 Vac, NEC Std, 3-ph | 15 |
| 600 Vac, Time Delay, 1-ph | 25 |
| 600 Vac, Time Delay, 3-ph | 50 |
| 125 Vdc | 5 |
| 250 Vdc | 10 |
| GSA Compliance | Yes |

Classifications

| | |
|------------|-----|
| cUL Listed | Yes |
| UL Listed | Yes |

Dimensions
by ABB

Dimensions

| | |
|--------|------|
| Height | 19.3 |
| Depth | 5.2 |
| Width | 9.4 |
| Weight | 23 |