



Representative Image

Catalog No. 9T21B1056G02**Description:** 1C,7.5kVA,240x480-120/240,115C,3R,QMS**UPC No** 783173803004**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	7.5 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
Sub Type	Standard
Frequency	50 Hz
FrameSize	16600
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R

Classifications

UL	Yes
cUL	Yes