



Representative Image

Catalog No. TLM3220CCUW

Description: 150/200A CONV LC 32-40 CRT N1 WHIT

UPC No 783164395907

Home > Load Centers > Load Centers

PowerMark Gold convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLM3220CCUW features space for 32, 1" breakers, a 200 A bus ampere rating, a copper bus, a white front, and a combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

Load Center Type	Standard
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	65
Amperage	200 A
Device type	Main Lug
Enclosure	Indoor
Phase	1 Phase
1" Space	32
1/2" Space	40
Feed	Either
Door	Yes
GSA Compliance	No
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 1
Factory Installed Ground Kit	No
# Branch Circuit 250A	32
Enclosure Type	Indoor, Combination
Wires	3 Wire
Service & Voltage	1 Phase, 3 Wire, 120/240V ac

Classifications

UL/CUL Listing	UL
----------------	----

Dimensions

Width	14.0 in
-------	---------

by ABB

Dimensions

Depth	3.8 in
-------	--------

Publications

Title	Publication No.	Publication Type
Section 1 BuyLog: Load centers and circuit breakers	DET1023	Application and Technical
Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line.		

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.