



Representative Image

**Catalog No. THQB31WY25****Description: THQB MCB SWITCH 3P 25A****UPC No 783164000603****Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers**

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. WY25 Amps 25 A

**Descriptors**

|              |                                   |
|--------------|-----------------------------------|
| Category     | Q-Line Miniature Circuit Breakers |
| Product Line | TEY / Q-Line (Bolt-On)            |
| GO Schedule  | EB                                |

**Specifications**

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Trip Style                      | Non-Interchangeable               |
| Frame Type                      | Q-Line                            |
| Amperage                        | 25 A                              |
| System Voltage                  | 120 Vac<br>120/240 Vac<br>240 Vac |
| Poles                           | 3                                 |
| Trip Function                   | LI                                |
| Continuous Current Rated        | Standard                          |
| 120 Vac Interrupting Rating     | 10 KAIC                           |
| 120/240 Vac Interrupting Rating | 10 KAIC                           |
| 240 Vac Interrupting Rating     | 10 KAIC                           |
| Suitable for Reverse Feed       | Yes                               |
| Long Time                       | No                                |
| Protective Relays               | No                                |
| Current Metering                | No                                |
| GSA Compliance                  | No                                |

**Classifications**

|           |        |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|

