



Representative Image

Catalog No. TM1615CCU

Description: 150A 16CT 1P3W 120/240V 22K IC COMB

UPC No 783164112528

Home > Load Centers > Load Centers

PowerMark Gold main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM1615CCU features spaces for 16, 1" breakers, a 150 A bus ampere rating, a copper bus, and a combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

Load Center Type	Standard
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Amperage	150 A
Device type	Main Breaker
Enclosure	Indoor
Phase	1 Phase
1" Space	16
1/2" Space	32
Feed	Either
Door	Yes
GSA Compliance	No
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 1
Factory Installed Ground Kit	No
# Branch Circuit 250A	16
Enclosure Type	Indoor, Combination
Wires	3 Wire
Service & Voltage	1 Phase, 3 Wire, 120/240V ac

Classifications

UL/CUL Listing	UL
----------------	----

Dimensions

Width	14.0 in
-------	---------

by ABB

Dimensions

Depth	3.7 in
-------	--------

Publications

Title	Publication No.	Publication Type
Section 1 BuyLog: Load centers and circuit breakers	DET1023	Application and Technical
Guide includes product features, photos, product number selection guide, knockout drawings, wiring diagrams, accessories and options list. Only available on-line.		

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.