



Representative Image

Catalog No. 1SVR508210R0100

Description: CT-SAC.22 Time relay, star-delta 2n/o, 24-48VDC/24-240VAC

UPC No 4013614534249

Home > Controls & Protective Relays > Time Relays

CT-SAC.22 Time relay, star-delta 2n/o, 24-48VDC/24-240VAC

Descriptors

Category	Time Relays
----------	-------------

Specifications

Rated Control Supply Voltage	24 ... 240 volt AC 24 ... 48 volt DC
Time Range	0.05 s ... 10 min
Product Main Type	CT-SAC
Output	2 n/o contacts
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	K
Ambient Air Temperature	Operation -20 ... +60 °C Storage -40 ... +85 °C
Analog Inputs	0
Connecting Capacity UL/CSA	Flexible 1x 18-14 AWG Rigid 1x 20-12 AWG Rigid 2x 20-16 AWG

Classifications

ETIM 5.0	EC001439 - Timer relay
ETIM 6.0	EC001439 - Timer relay
ETIM 7	EC001439 - Timer relay
eClass	7.0 27371790

Dimensions

Product Net Width	17.5 mm
Product Net Height	80 mm
Product Net Depth / Length	63 mm
Product Net Weight	0.066 kg

Package Information

Package Level 1 Units	1 piece
-----------------------	---------

Package Information

Package Level 1 Width	89 mm
Package Level 1 Depth / Length	20 mm
Package Level 1 Height	65 mm
Package Level 1 Gross Weight	0.079 kg
Package Level 1 EAN	4013614534249

Ordering

Minimum Order Quantity	1
Customs Tariff Number	85364900
ECCN	N
ECN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)
ABB Business Unit	ELSP - Smart Power