



Representative Image

Catalog No. RMS112522LRGR

Description: MTR STACK 5-225A 1PH-1PH RING SKT 10-22K

UPC No 783164683639

Home > Modular Metering > ReliaMod&Trade; > ReliaMod Meter Module

Descriptors

Category	ReliaMod Meter Module
----------	-----------------------

Specifications

Additional Notes	For tenant breaker load lugs, please refer to breaker specifications
Depth (Inches)	9.6
Enclosure	N3R Outdoor
Estimated Weight (lbs)	221
Height (Inches)	83.9
Horizontal Bus Amperage	1200 A
Main Phase Input	1-Phase
Meter Mod III to ReliaMod Horizontal Bus Connections	ABB ReliaMod horizontal bus does not match up to GE Meter Mod III horizontal bus, so any ReliaMod section cannot be connected to any GE Meter Mod III section and vice versa without a bus transition adapter section. Please refer to the ReliaMod bus transition adapters in the Buylog for more information.
Meter Module Tenant Breaker Provisions	Only Accepts 10-22 KAIC Formula A1 & A2 Tenant Breakers
No of Sockets	5
Socket Amperage	225 A
Socket Bypass	None
Socket Factory Installed Jaw Configuration	4-Jaw
Socket Phase Output	1-Phase
Socket Type	Ring Type
Tenant Ground Lugs (Per each socket) AWG/kcmil Al/Cu	#14-2/0
Tenant Neutral Lugs (Per each socket) AWG/kcmil Al/Cu	#6-300
Voltage	120/240V
Width (Inches)	18.4

by ABB