



Representative Image

Catalog No. TSMR2020CSCUFMG**Description: MSLC MB Rgls 200A 20/40 S UGOH MEG****UPC No 783164415179****Home > Load Centers > Meter Socket Load Center**

PowerMark Gold Meter Socket Load Centers are an ideal option for residential applications. Additionally, PowerMark Gold Meter Socket Load Centers provide increased reliability and maximum circuit layout flexibility. All our PowerMark Gold Meter Socket Load Centers are built with high-quality materials for extended durability. Furthermore, their perfected design allows for an easy and fast installation. The TSMR2020CSCUFMG is a ringless main breaker meter socket features spaces for 20, 1" breakers, a 200A main ampere rating, a copper bus, and an outdoor suitable enclosure.

Descriptors

Category	Meter Socket Load Center
GO Schedule	RB
Grouping	Meter Socket

Specifications

Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Amperage	200 A
Enclosure	Outdoor
Phase	1 Phase
1" Space	20
1/2" Space	40
Feed	Either
Door	Yes
GSA Compliance	No
Circuit Breaker Style	Plug-In
NEMA Rating	NEMA 3R
Factory Installed Ground Kit	Yes
Enclosure Type	OutdoorType 3R
Wires	3 Wire
Service & Voltage	1 Phase, 3 Wire, 120/240V ac

Classifications

UL/CUL Listing	UL
----------------	----

Dimensions

Width	14.0 in
Depth	4.5 in