

**Alternate Catalog No. SU201M-C25**  
**Catalog No. 2CDS271337R0254**

**Description:** UL489 MCB 1P C 25A 480/277

**UPC No** 4016779930895

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU201M-C25 Miniature Circuit Breaker C-Char., 10kA, 25A, 1P UL489



Representative Image

**Descriptors**

|          |                            |
|----------|----------------------------|
| Category | UL 489 Branch Circuit MCBs |
|----------|----------------------------|

**Specifications**

|                                                |                                                       |
|------------------------------------------------|-------------------------------------------------------|
| Number of Poles                                | 1                                                     |
| Tripping Characteristic                        | C                                                     |
| Rated Current                                  | 25 A                                                  |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489            |
| Product Main Type                              | SU200M                                                |
| Rated Voltage (V)                              | (277 V AC)<br>(48 V DC)                               |
| Interrupting Rating acc. to UL489              | (277 V AC) 10 kA<br>(48 V DC) 10 kA                   |
| Rated Ultimate Short-Circuit Breaking Capacity | (230 V AC) 15 kA                                      |
| Power Loss                                     | 3,2 W<br>at Rated Operating Conditions per Pole 3,2 W |