



Representative Image

Catalog No. 9T21B1253G02

Description: "1A,3kVA,575>200-115/230,115C,3R,50Hz,QMS"

UPC No 783173129203

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

Specifications

Phase	1
PriVoltage	200/220/380/400/416/460/575
SecVoltage	115/230
KVA	3.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
Sub Type	Standard
Frequency	50 Hz
Impedance	0.00 %
FrameSize	16350
Net Weight	103
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	103
Taps	(-1 TAPS)
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	10.6 in
Depth	11.0 in
Height	14.5 in