

**Alternate Catalog No. PSR85-600-11**  
**Catalog No. 1SFA896114R1100**

**Description:** "PSR SSTR,600V/24V AC/DC,80A"

**UPC No** 7320500477250

**Home > Soft Starters > Softstarter - Open (PSR)**

**PSR softstarter - The compact range**The PSR softstarter range is a simple yet reliable starting solution that utilizes only the most basic of soft starting features: soft start and stop. It performs well in applications requiring many starts per hour and is perfect for installations where you need to save space.**Main benefits\*** Small and compact starting solution\* Can perform many starts per hour\* Reduce energy loss at full speed with built-in bypass.**Main features\*** Rated operational current: 3 to 105 A\* Operational voltage: 208-600 V AC\* Control supply voltage: 24 V AC/DC or 100-240 V AC.



Representative Image

**Descriptors**

|          |                          |
|----------|--------------------------|
| Category | Softstarter - Open (PSR) |
|----------|--------------------------|

**Specifications**

|                                       |               |
|---------------------------------------|---------------|
| Product Type                          | Soft Starters |
| Input Voltage                         | 208-600 V     |
| Control Voltage                       | 24Vac/dc      |
| Normal Duty: Output Current (A)       | 80            |
| Normal Duty: Motor Power (HP) at 460V | 60            |
| Power Dissipation In Watts            | 7.2           |
| Height (Inches)                       | 8.7           |
| Width (Inches)                        | 2.8           |
| Depth (Inches)                        | 7.1           |

**Classifications**

|                |     |
|----------------|-----|
| RoHS Indicator | Yes |
| UL/CUL Listing | Yes |

**Dimensions**

|             |     |
|-------------|-----|
| Weight (lb) | 5   |
| Height (mm) | 220 |
| Width (mm)  | 70  |
| Depth (mm)  | 180 |
| Weight (kg) | 2.3 |

