



Representative Image

Alternate Catalog No. PSTX105-690-70
Catalog No. 1SFA898209R7000

Description: SOFTSTARTER

UPC No 7320500501344

Home > Soft Starters > Softstarter - Open (PSTX)

Descriptors

Category	Softstarter - Open (PSTX)
----------	---------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-690 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	104
Normal Duty: Motor Power (HP) at 208V	30
Normal Duty: Motor Power (HP) at 230V	40
Normal Duty: Motor Power (HP) at 460V	75
Normal Duty: Motor Power (HP) at 575V	100
Heavy Duty: Output Current (A)	80
Heavy Duty: Motor Power (HP) at 208V	25
Heavy Duty: Motor Power (HP) at 230V	30
Heavy Duty: Motor Power (HP) at 460V	60
Heavy Duty: Motor Power (HP) at 575V	75
Power Dissipation In Watts	10
Height (Inches)	12.4
Width (Inches)	5.9
Depth (Inches)	7.7

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Weight (lb)	13.4
Height (mm)	314
Width (mm)	150
Depth (mm)	197.5

Dimensions	
Weight (kg)	6.1