



Catalog No. CMP250-4-A

Description: SHRINK-KON-1,22M

UPC No 5414363102557

Home > Connectivity & Grounding > Shrink-Kon > Heat shrinkable tube

Heat Shrink Tubing, 6.4mm, Yellow, 1.22m Cut Length, 25 per box

Representative Image

Descriptors

Category	Heat shrinkable tube
----------	----------------------

Specifications

Shrink Ratio	2:1
Color	Yellow

Classifications

Brand Name	Shrink-Kon
------------	------------

Dimensions

Thickness	Thin
Length	492.1 ft , 150 m

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 233 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	6.4 mm
Inner diameter before heat-shrink	0.25 inch
Inner diameter after heat-shrink	3.2 mm
Inner diameter after heat-shrink	0.126 inch
Nominal diameter inch	1/4 inch

by ABB

ETIM	EC000217 Shrink tubing
Wall thickness after shrinking	0.6 mm
Wall thickness after shrinking	0.02 inch
Length	1.22 m
Length	4 ft
Operation temperature	-55-+135 °C
Operation temperature	-67-+275 °F
Colour	Yellow
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y