



Representative Image

Catalog No. DBRF630706000

Description: 60A,ILK,3P4W,MG,307,125/250V,FC

UPC No 708917305170

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Receptacle with Circuit Breaker, 60 Amp, 3 Pole 4 Wire, 125/250V, 60Hz, Breaker Trip Rating 60 Amp

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	60 Amps
Voltage Rating	250 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	60 A
Number of poles	3