



Representative Image

Catalog No. DBRS350403000

Description: 30A,ILK,4P5W,MG,504,3PY277/480,SC

UPC No 708917306641

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

MaxGard Interlocked Receptacle with Circuit Breaker with Screw Cap, 30 Amp, 4 Pole 5 Wire, 3 Phase Y 277/480V, 60Hz, Breaker Trip Rating 30 Amp

Descriptors

Category	Electrical receptacles
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

Specifications

Material	Cast Aluminum
----------	---------------

Classifications

Brand Name	Russellstoll
------------	--------------

FTIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Number of poles	4