



Representative Image

Catalog No. DF1516FR00K

Description: 100A,REC,4P5W,MG,516,00K,3PY120

UPC No 708917047513

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Flap Cap Receptacle with Control Contacts, 100 Amp, 4 Pole 5 Wire, 30Y 120/208V, 60Hz

| Descriptors       |  |
|-------------------|--|
| Category          | Electrical sleeves   |
| Special Features  | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application       | Convention centers and areanas   |
| Specifications    |  |
| Number Of Poles   | 4  |
| Number Of Wires   | 5  |
| Amperage Rating   | 100 Amps   |
| Material          | Cast Aluminum  |
| Classifications   |  |
| Brand Name        | Russellstoll   |
|                   |  |
| ETIM              | EC001322 Round socket/plug for high currents   |
| Amperage          | 100 A  |
| Construction type | Wall socket  |
| Number of poles   | 4  |