



Representative Image

Catalog No. DF2504FRAB0/C200

Description: 200A,REC,4P5W,504,AB0,3P277V,2IN@C

UPC No 708917333425

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Flap Cap Receptacle with Angle Adapter and Junction Box, 200 Amp, 4 Pole 5 Wire, 30Y 277/480V, 60Hz, with 2 Inch NP at C

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	200 Amps
Voltage Rating	480 V

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Construction type	Wall socket
Number of poles	4