



Representative Image

## Catalog No. DF2504FRABK

**Description:** 200A,REC,4P5W,MG,504,ABK,3PY277

**UPC No** 708917274896

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Female Receptacle with Angle Adapter and Junction Box and Control Contacts, 200 Amp, 4 Pole 5 Wire, 30Y 277/480V, 60Hz

### Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Electrical hook-up of mobile medical imaging (MMI) trailers.

### Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	200 Amps
Voltage Rating	277 V
Material	Cast Aluminum

### Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Construction type	Wall socket
Number of poles	4