



Representative Image

Catalog No. DF3307FRAB0

Description: 30A,REC,3P4W,MG,307,AB0,125/250

UPC No 708917172147

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

MaxGard Female Receptacle with Angle Adapter and Junction Box, 30 Amp, 3 Pole 4 Wire, 125/250V, 60Hz

Descriptors

Category	Electrical receptacles
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport.

Specifications

Material	Cast Aluminum
----------	---------------

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Wall socket
Number of poles	3