



Representative Image

Catalog No. DF3307FRABK

Description: 30A,REC,3P4W,MG,307,ABK,125/250

UPC No 708917313601

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Flap Cap Receptacle with Angle Adapter, Junction Box and Control Contacts, 30 Amp, 3 Pole 4 Wire, 125/250V, 60Hz

Descriptors

| | |
|------------------|---|
| Category | Electrical sleeves |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application | For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport. |

Specifications

| | |
|-----------------|---------------|
| Number Of Poles | 3 |
| Number Of Wires | 4 |
| Amperage Rating | 30 Amps |
| Material | Cast Aluminum |

Classifications

| | |
|-------------------|--|
| Brand Name | Russellstoll |
| ETIM | EC001322 Round socket/plug for high currents |
| Amperage | 30 A |
| Construction type | Wall socket |
| Number of poles | 3 |