



Representative Image

Catalog No. DF3316FR000

Description: 30A,REC,3P4W,MG,316,120/208

UPC No 708917168720

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

Maxgard Female Receptacle, 30Amp, 3 Pole 4 Wire, 120/208V, 60Hz

Descriptors

Category	Electrical receptacles
----------	------------------------

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Voltage Rating	208 V

Classifications

Brand Name	Russellstoll
Sub Brand	MaxGard

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Wall socket
Number of poles	3