



Representative Image

Catalog No. DF3316FR00K

Description: 30A,REC,3P4W,MG,316,00K,120/250

UPC No 708917200055

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Female Receptacle, Voltage 120/208V, Amperage 30A, 3 Poles 4 Wire, with Flap Cap and 2 Control Contacts

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Voltage Rating	120/208 V
Color	Gray

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Wall socket
Number of poles	3