



Representative Image

Catalog No. DS3316FRA0K

Description: 30A,REC,3P4W,MG,316,AGL,120/208,CC

UPC No 708917312154

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Receptacle with Angle Adapter and Control Contacts, 30 Amp, 3 Pole 4 Wire, 120/208V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport.

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Number of poles	3