



Representative Image

Catalog No. DS4516FRAB0/A400

Description: 400A,REC,4P5W,MG,516,AB0,3P208V,SC

UPC No 708917299844

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Receptacle with Angle Adapter and Junction Box, 400 Amp, 4 Pole 5 Wire, 30Y 120/208V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Shore power to marine vessels-sightseeing boats

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	400 Amps
Voltage Rating	208 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	400 A
Number of poles	4