



Representative Image

Catalog No. DSR6504NA000/E125

Description: 60A ILK 4P5W MG 3PY277V 1.25 IN @E

UPC No 708917311522

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Interlocked Receptacle with Switch, 60 Amp, 4 Pole 5 Wire, 30Y 277/480V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Power for trade show exhibits and concerts, Electrical hook-up of mobile medical imaging (MMI trailers)

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	60 Amps
Voltage Rating	277 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	60 A
Number of poles	4