



Catalog No. LR100MCG

Description: LR100M WITH COVER AND GASKET

UPC No 786209868770

Home > Cable Protection Systems > T&B Rigid Fittings > Electrical conduit fitting body

1 Inch Series 35 Unipak Type LR Conduit Body, Cover and Gasket, Body Material and Finish Malleable Iron Zinc Plated with Aluminum, Acrylic Coating, Cover Material and Finish Stamped Steel Zinc Plated, Gasket Material Neoprene

Descriptors

Category	Electrical conduit fitting body
Special Features	Zinc-Plated Iron Construction with Aluminum Acrylic Coating Provides Durability, Impact Resistance and Corrosion Resistance.
Application	To Connect Conduit Sections

Specifications

Material	Malleable Iron
Finish	Zinc Plating with Aluminum Acrylic Coating

Classifications

Brand Name	T&B Rigid Fittings
Standard	UL E2969

Dimensions

Hub Size	1 in
----------	------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC003618 Form part for installation tubes
Model	Bend type LR (Canada)
Material	Metal
Material quality	Other