

Catalog No. MLP750-6-A

Description: HTSHK 2:1 BLUE 3/4IN EXPDIA 1.22M

UPC No 5414363105619

Home > Connectivity & Grounding > Shrink-Kon > Heat shrinkable tube

Heat Shrink Tubing, Flexible for High Specifications, UL/CSA Listed, Thin Wall, Shrink Ratio 2:1, 3/4 Inch/19.1mm Expanded Diameter, Blue, 10 X 1.22M Lengths

Representative Image

Descriptors

Category	Heat shrinkable tube
----------	----------------------

Specifications

Shrink Ratio	2:1
Flammability	Flame Retardant
Color	Blue

Classifications

Brand Name	Shrink-Kon
------------	------------

Dimensions

Thickness	Thin
Length	4 ft , 1.22 m

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000217 Shrink tubing
Type	Heat-shrink
Model	Thin-walled
Shrink rate	2:1
Inner diameter before heat-shrink	19.1 mm
Inner diameter before heat-shrink	0.75 inch
Inner diameter after heat-shrink	9.5 mm
Inner diameter after heat-shrink	0.37 inch

by ABB

ETIM	EC000217 Shrink tubing
Nominal diameter inch	3/4 inch
Wall thickness after shrinking	0.8 mm
Wall thickness after shrinking	0.03 inch
Length	1.22 m
Length	4 ft
Operation temperature	-55-+135 °C
Operation temperature	-67-+275 °F
Colour	Blue
Material	Polyolefin (PO-X)
Halogen free	N
With inner glue	N
Printable	N
UL approval	Y