



Catalog No. PAC1612R

Description: LD CTR CONV 125A 16/32 AL N3R GR PON UL

UPC No 783164701289

Home > Load Centers > Load Centers

ABB ReliaHome makes homes reliable, with ease. We designed our ReliaHome load centers to be installed as fast as possible - and reliable so your customers can leave a job with confidence. They work seamlessly with all our residential circuit breakers, optimizing your stock.

Descriptors

Category	Load Centers
GO Schedule	RT
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	16
1" Space	16
1/2" Space	0
Amperage	125 A
Circuit Breaker Style	Plug-On Neutral
Door	Yes
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	Yes
Feed	Top
Input/Output Voltage	120/240V ac
Interrupt Rating	22kAIC
Interrupting Capacity Rating	22kAIC
Load Center Type	P-Series (PON)
Meter Socket Options: 200 Amp Main Breaker Installed	No
Meter Socket Options: High Amp Mode	None
NEMA Rating	NEMA 3R
No of Circuits	32
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----