



Catalog No. RA863UFR

Description: NYLON RNG 22-18 No8 BOLT 45 DEG REV

UPC No 786209995599

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Nylon Insulated Ring Terminal with 45 Degree Backward Bend, Length .89 Inches, Width .26 Inches, Maximum Insulation .136, Bolt Hole #8, Wire Range #22-#16 AWG, Color Red, Copper, Tin Plated, 1,000 Pack

Descriptors

Category	Electrical terminals
----------	----------------------

Specifications

Material	Nylon
Color	Red

Classifications

Brand Name	Sta-Kon
------------	---------

Dimensions

Wire Size	22-16 AWG
-----------	-----------

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Red
Reel packaging	N
AWG-range	22-16
Material	Copper
Surface protection	Tinned
Stud size (imperial)	8