



Representative Image

Catalog No. RBC717M

Description: VNYL INS HVDTY RNG TERM 16-14 TAPE

UPC No 786210187938

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Vinyl Insulated Heavy-Duty Ring Terminal, Length 1.19 Inches, Width .51 Inches, Maximum Insulation .210, Bolt Hole 1/4 Inch, Wire Range #16-#14 Heavy Duty AWG, Color Blue, Copper, Tin Plated, On Mylar Tape, 500 Pack

Descriptors

Category	Electrical terminals
----------	----------------------

Specifications

Material	Vinyl
Color	Blue

Classifications

Brand Name	Sta-Kon
------------	---------

Dimensions

Wire Size	16-14 AWG
-----------	-----------

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	Polyvinyl chloride (PVC)
Colour insulation	Blue
Reel packaging	Y
AWG-range	16-14
Material	Copper
Surface protection	Tinned
Stud size (imperial)	1/4 inch