



Catalog No. TLMQ812SCUD

Description: 8CIRC MNLUG 125A INDOOR SURFC W/DR

UPC No 783164680720

Home > Load Centers > Load Centers

ReliaHome T-Series convertible load centers arrive as main lug, but have the capability to have a main breaker installed. All ABB load centers are rated up to 60 degree/75 degree centigrade and is suitable for use with service entrance equipment when installed in accordance with electrical code. The TLMQ812SCUD features space for 8, 1" breakers, 125 A bus ampere rating, a copper bus, an optional door for 6-8 circuit panel, a factory installed ground bar, and a surface enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	8
1" Space	8
1/2" Space	0
Amperage	125 A
Circuit Breaker Style	Pigtail (non-PON)
Device type	Main Lug
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Combination
Factory Installed Ground Kit	Yes
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Load Center Type	T-Series (non-PON)
Meter Socket Options: 200 Amp Main Breaker Installed	No
Meter Socket Options: High Amp Mode	None
NEMA Rating	NEMA 1
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----


by ABB