



Catalog No. TMQ830RCUGEN

Description: 50A DUAL MAIN BREAKER GENERATOR PNL

UPC No 783164681079

Home > Load Centers > Load Centers

ReliaHome generator panels maintain power to such critical circuits as those for furnace, pump, refrigerator, and lights. It features a connected dual breaker mechanism that ensures that only one source is active at a time. Generator panels ensure safety and convenience when using a generator; with a 14,000 peak wattage, 11,520 continuous load, and 48 amps at 240 volts. The TMQ830FCUGEN features a main breaker, spaces for 8, 1" breakers, a 30A main bus ampere, a copper bus, and a flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RD
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	4
1" Space	4
1/2" Space	0
Amperage	30 A
Circuit Breaker Style	Pigtail (non-PON)
Device type	Main Breaker
Door	Yes
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface Mount
Factory Installed Ground Kit	Yes
Feed	Either
Input/Output Voltage	120/240V ac
Interrupting Capacity Rating	22
Load Center Type	Generator
Meter Socket Options: 200 Amp Main Breaker Installed	No
Meter Socket Options: High Amp Mode	None
NEMA Rating	NEMA 3R
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing

UL

by ABB