



Representative Image

Catalog No. YPS322520

Description: BLACK Y PIECE 32X25X20 NYLON

UPC No 5020963022173

Home > Cable Protection Systems > Harnessflex > Electrical conduit elbow

Hinged Conduit Joiner, Y-Shape, Conduit Size A: NC32/NW29, Size B: NC25/NW22, Size C: NC20/NW17, Operating Temperature -40 to 120 Degrees Celsius, RoHS Compliant, IP40 Rating, Very High UV Protection, Polyamide (Nylon), Black

Descriptors

Category	Electrical conduit elbow
Special Features	Can Be Use as an In-Line Reducer as well as Enlarger
Application	Designed to Snap Together Over All Types of Slit and Unslit Conduit, Maintaining Maximum Conduit Bore

Specifications

Material	Polyamide/Nylon
Color	Black
Flexibility	Rigid

Classifications

Brand Name	Harnessflex
Standard	RoHS, Conforms with End of Life Vehicle Directive (ELV) EU200/53/EC

Dimensions

Size	Conduit Sizes A: NC32/NW29, B: NC25/NW22, C: NC20/NW17
------	--

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001172 Coupler for corrugated plastic hoses
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP40
Model	Y-piece
Nominal size	20-32 mm
Colour	Black

