



Representative Image

**Catalog No. 9T51B0593****Description:** 1C,3kVA,600-120/240,115C,3R,50/60Hz,QB**UPC No** 783173037041**Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

**Descriptors**

|             |                                           |
|-------------|-------------------------------------------|
| Category    | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T5                                        |

**Specifications**

|                |          |
|----------------|----------|
| Phase          | 1        |
| PriVoltage     | 600      |
| SecVoltage     | 120/240  |
| KVA            | 3.0 KVA  |
| Coil Material  | CU       |
| TempRise       | 115.0 °C |
| ElecShield     | N        |
| Sub Type       | Standard |
| Frequency      | 50 Hz    |
| FrameSize      | 14400    |
| TempClass      | 180.0 °C |
| AmbTemp        | 40.0 °C  |
| InsulSys       | IS-12    |
| KFactor        | K1       |
| Enclosure Type | NEMA 3R  |

**Classifications**

|     |     |
|-----|-----|
| UL  | Yes |
| cUL | Yes |