

**Alternate Catalog No. S202MUC-K8**  
**Catalog No. 2CDS272061R0407**

**Description: MCB S200MUC 2P K 8A AC/DC**

**UPC No 4013614433191**

**Home > Circuit Breakers > Miniature Circuit Breakers > Supplementary Protectors**

The miniature circuit breaker S 200 M UC extends the established ABB System pro M compact® product range with an MCB for DC and AC applications. The S 200 M UC impresses with its performance range and the accordingly large amount of approvals. Its high inbuilt short circuit breaking capacity across the entire model line, its flexible AC and DC application and its approval and compliance in accordance with all major international and local standards make it truly unique. All current System pro M compact® accessories can be combined easily with the new model line. Whether warehousing or project engineering, planning, installing or maintaining your equipment, the S 200 M UC is a simple and flexible solution.

Representative Image

**Descriptors**

|          |                          |
|----------|--------------------------|
| Category | Supplementary Protectors |
|----------|--------------------------|

**Specifications**

|                                                |                                                          |
|------------------------------------------------|----------------------------------------------------------|
| Number of Poles                                | 2                                                        |
| Tripping Characteristic                        | K                                                        |
| Rated Current                                  | 8 A                                                      |
| Standards                                      | CSA 22.2 No. 235<br>IEC/EN 60947-2<br>UL 1077            |
| Product Main Type                              | S200MUC                                                  |
| Rated Voltage (V)                              | (500 V DC)<br>(480Y / 277 V AC)                          |
| Interrupting Rating acc. to UL1077             | (500 V DC) 10 kA<br>(480Y / 277 V AC) 6 kA               |
| Rated Ultimate Short-Circuit Breaking Capacity | (220 V DC) 25 kA<br>(440 V AC) 10 kA<br>(440 V DC) 10 kA |
| Power Loss                                     | 2.5 W<br>at Rated Operating Conditions per Pole 1.26 W   |