



Representative Image

Alternate Catalog No. PSE30-600-70
Catalog No. 1SFA897103R7000

Description: SOFTSTARTER

UPC No 7320500400616

Home > Soft Starters > Softstarter - Open (PSE)

PSR softstarter - The compact rangeThe PSR softstarter range is a simple yet reliable starting solution that utilizes only the most basic of soft starting features: soft start and stop. It performs well in applications requiring many starts per hour and is perfect for installations where you need to save space.**Main benefits*** Small and compact starting solution* Can perform many starts per hour* Reduce energy loss at full speed with built-in bypass.**Main features*** Rated operational current: 3 to 105 A* Operational voltage: 208-600 V AC* Control supply voltage: 24 V AC/DC or 100-240 V AC.

Descriptors

Category	Softstarter - Open (PSE)
----------	--------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	100-240 V
Normal Duty: Output Current (A)	28
Normal Duty: Motor Power (HP) at 208V	7.5
Normal Duty: Motor Power (HP) at 230V	10
Normal Duty: Motor Power (HP) at 460V	20
Normal Duty: Motor Power (HP) at 575V	25
Heavy Duty: Output Current (A)	25
Heavy Duty: Motor Power (HP) at 208V	7.5
Heavy Duty: Motor Power (HP) at 230V	7.5
Heavy Duty: Motor Power (HP) at 460V	15
Heavy Duty: Motor Power (HP) at 575V	20
Power Dissipation In Watts	0.50
Height (Inches)	9.6
Width (Inches)	3.5
Depth (Inches)	7.2

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Weight (lb)	5.3
Height (mm)	245
Width (mm)	90
Depth (mm)	183.5

Dimensions

Weight (kg)

2.4