



Catalog No. 9T10A1452

Description: "3A,30kVA,208-208Y,150C,N2,K1,DOE"

UPC No 783173901007

Home > Transformers > Dry Type Vented > General Purpose

ABB's Low Voltage Dry Type transformers are built to last and are designed with exclusive features. With easy installation and all of the specifications you trust, it's easy to see why ABB QL dry type transformers are preferred by contractors. Our Type QL transformers meet DOE efficiency standards. They are available with aluminum or copper windings and in all three temperature rise ratings.

Descriptors

Category	General Purpose
GO Schedule	TY

Specifications

TransType	DOE 2016
Phase	3
PriVoltage	208
SecVoltage	208Y/120
KVA	30.0 KVA
Coil Material	AL
TempRise	150.0 °C
Frequency	60 Hz
Impedance	5.0 %
AmbTemp	40.0 °C
EnergyEfficiency	DOE 2016
KFactor	K1
Enclosure Type	NEMA 2
Sound	Std

Classifications

CE	0
----	---