



Representative Image

Catalog No. TM12RMCFMG**Description:** MtrMain Rgls 125A S 0/0 Ct OH/UG N3R MEG**UPC No** 783164244618**Home > Load Centers > Meter Socket Load Center**

PowerMark Gold Meter Socket Load Centers are an ideal option for residential applications. Additionally, PowerMark Gold Meter Socket Load Centers provide increased reliability and maximum circuit layout flexibility. All our PowerMark Gold Meter Socket Load Centers are built with high-quality materials for extended durability. Furthermore, their perfected design allows for an easy and fast installation. The TM12RMCFMG is a ringless meter main and features a 400 A main ampere rating and an outdoor suitable, surface enclosure.

Descriptors

Category	Meter Socket Load Center
Grouping	Meter Socket

Specifications

Input/Output Voltage	120/240V ac
Amperage	125 A
Enclosure	Outdoor
Phase	1 Phase
1" Space	0
1/2" Space	0
NEMA Rating	NEMA 3R
Factory Installed Ground Kit	No
Enclosure Type	Outdoor, Surface Mount

Classifications

UL/CUL Listing	UL
----------------	----